



WXP0112

## Plate gallery plastic plastic 2 gang horizontal 71mm titane

### Technical properties

#### Architecture

Fixing mode Clipped

#### Dimensions

Depth 9.3 mm

Height 88 mm

Width 163 mm

#### Capacity

Number of sockets 2

#### Materials

Free area for finishing name titane

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Surface appearance matt

Type of surface treatment Painted

#### Installation, mounting

Mounting way horizontal

#### Equipment

With transparent product label holder No

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts 05

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition Surface mounted frame