



WXP0612

Plate gallery plastic plastic 2 gang horizontal 71mm eglantine

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 88 mm

Width 163 mm

Capacity

Number of sockets 2

Materials

Free area for finishing name eglantine

Colour red (shades)

RAL colour RAL 3012 - Beige red

Material Polycarbonate (PC)

Surface appearance matt

Type of surface treatment Painted

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

