



WXP0706

## Plate gallery plastic plastic 6 modules enteraxe 57mm river

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	9.3 mm
-------	--------

Height	88 mm
--------	-------

Width	206 mm
-------	--------

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Free area for finishing name	river
------------------------------	-------

Material	Polycarbonate (PC)
----------	--------------------

Surface appearance	matt
--------------------	------

Type of surface treatment	Painted
---------------------------	---------

#### Installation, mounting

Mounting way	horizontal
--------------	------------

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP21
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

#### Use conditions

Operating temperature	-10...35 °C
-----------------------	-------------

Storage/transport temperature	-10...50 °C
-------------------------------	-------------