



WXP0806

**Plate gallery plastic plastic 6 modules enteraxe 57mm peacock**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Dimensions**

Depth	9.3 mm
Height	88 mm
Width	206 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Free area for finishing name	peacock
Colour	green (shades)
Surface appearance	matt
Type of surface treatment	Painted

**Installation, mounting**

Mounting way	horizontal
--------------	------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Composition	Surface mounted frame
-------------	-----------------------