



WXP1012

**Plate gallery plastic plastic 2 gang horizontal 71mm anthracite**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Dimensions**

Depth	9.3 mm
Height	88 mm
Width	163 mm

**Capacity**

Number of sockets	2
-------------------	---

**Materials**

Free area for finishing name	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	Painted

**Installation, mounting**

Mounting way	horizontal
--------------	------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C