



WXP2202

### Plate gallery 1 gang bronze leaf

#### Technical properties

##### Architecture

Fixing mode Clipped

##### Dimensions

Depth 9.3 mm

Height 88 mm

Width 92 mm

##### Capacity

Number of sockets 1

##### Materials

Free area for finishing name bronze

Surface appearance matt

##### Installation, mounting

Mounting way horizontal

##### Equipment

With transparent product label holder No

##### Standards

European directive WEEE not concerned

##### Safety

IK protection code against mechanical impacts 05

RoHS conform Yes

##### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

##### Identification

Range gallery

Composition Surface mounted frame