



WXP2412

## Plate gallery 2 gang horizontal 71mm pecan

### Technical properties

#### Architecture

Fixing mode Clipped

#### Dimensions

Depth 9.3 mm

Height 88 mm

Width 163 mm

#### Capacity

Number of sockets 2

#### Materials

Free area for finishing name pecan

Colour dark wood optics

RAL colour RAL 8025 - Pale brown

Material wood

Surface appearance matt

Type of surface treatment Untreated

#### Installation, mounting

Mounting way horizontal

#### Equipment

With transparent product label holder No

#### Standards

European directive WEEE not concerned

#### Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

RoHS conform Yes

#### Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

#### Identification

Range gallery

Composition Surface mounted frame