



WXP2413

Plate gallery 3 gang horizontal 71mm pecan

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

Dimensions

| | |
|--------|--------|
| Depth | 9.3 mm |
| Height | 88 mm |
| Width | 234 mm |

Capacity

| | |
|-------------------|---|
| Number of sockets | 3 |
|-------------------|---|

Materials

| | |
|--------------------|------|
| Surface appearance | matt |
|--------------------|------|

Installation, mounting

| | |
|--------------|------------|
| Mounting way | horizontal |
|--------------|------------|

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|-----|
| IK protection code against mechanical impacts | 05 |
| RoHS conform | Yes |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-------------|-----------------------|
| Range | gallery |
| Composition | Surface mounted frame |