



WXP4205

Plate gallery 5 modules enteraxe 71mm bright inox material

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 87.7 mm

Width 163 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name bright inox

Surface appearance matt

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame