



WXP4206

Plate gallery 6 modules enteraxe 57mm bright inox material

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 87.7 mm

Width 206 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name bright inox

Colour stainless steel optics

RAL colour RAL 9007 - Grey aluminium

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

Installation, mounting

Mounting way horizontal

Equipment

With transparent product label holder No

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

Protection index IP IP21

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame