



WXP4302

## Plate gallery 1 gang natural alu material

### Technical properties

#### Architecture

Fixing mode	Clipped
-------------	---------

#### Dimensions

Depth	9.3 mm
Height	87.7 mm
Width	92 mm

#### Capacity

Number of sockets	1
-------------------	---

#### Materials

Free area for finishing name	natural alu
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material	Aluminium
Surface appearance	matt
Type of surface treatment	brushed

#### Installation, mounting

Mounting way	horizontal
--------------	------------

#### Equipment

With transparent product label holder	No
---------------------------------------	----

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C