



WXP4306

**Plate gallery 6 modules enteraxe 57mm natural alu material**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Dimensions**

Depth	9.3 mm
Height	87.7 mm
Width	206 mm

**Capacity**

Number of sockets	1
-------------------	---

**Materials**

Free area for finishing name	natural alu
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material	Aluminium
Surface appearance	matt
Type of surface treatment	brushed

**Installation, mounting**

Mounting way	horizontal
--------------	------------

**Equipment**

With transparent product label holder	No
---------------------------------------	----

**Standards**

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

IK protection code against mechanical impacts	05
---	----

**Use conditions**

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

**Identification**

Composition	Surface mounted frame
-------------	-----------------------