



WXP4314

Plate gallery 4 gang horizontal 71mm natural alu material

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	87.7 mm
Width	305 mm

Capacity

Number of sockets	4
-------------------	---

Materials

Free area for finishing name	natural alu
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material	Aluminium
Surface appearance	matt
Type of surface treatment	brushed

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C