



WXP4606

Plate gallery 6 modules enteraxe 57mm copper alu material

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	87.7 mm
Width	206 mm

Capacity

Number of sockets	1
-------------------	---

Materials

Free area for finishing name	copper alu
Colour	copper optics
Material	Aluminium
Surface appearance	matt
Type of surface treatment	brushed

Installation, mounting

Mounting way	horizontal
--------------	------------

Equipment

With transparent product label holder	No
---------------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP21

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C