



WXP4612

Plate gallery 2 gang horizontal 71mm copper alu material

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Dimensions

Depth	9.3 mm
Height	87.7 mm
Width	163 mm

Capacity

Number of sockets	2
-------------------	---

Materials

Free area for finishing name	copper alu
Surface appearance	matt

Installation, mounting

Mounting way	horizontal
--------------	------------

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-10...35 °C
Storage/transport temperature	-10...50 °C

Identification

Range	gallery
Composition	Surface mounted frame