



WXP4802

Plate gallery 1 gang grey wood material

Technical properties

Architecture

Fixing mode Clipped

Dimensions

Depth 9.3 mm

Height 87.7 mm

Width 92 mm

Capacity

Number of sockets 1

Materials

Free area for finishing name grey wood

Surface appearance matt

Installation, mounting

Mounting way horizontal

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 05

RoHS conform Yes

Use conditions

Operating temperature -10...35 °C

Storage/transport temperature -10...50 °C

Identification

Range gallery

Composition Surface mounted frame