



ED183

Intensity relay

Technical properties

Frequency

Frequency	50 - 50 Hz
-----------	------------

Capacity

Number of modules	1
-------------------	---

Use conditions

Operating temperature	-20 - +40 °C
Storage/transport temperature	-40 - +90 °C

Endurance

Electric endurance in number of cycles	10,000,000
--	------------

Dimensions

Height	83 mm
Width	17.80 mm
Depth	60 mm

Electric current

Operating current	7 - 39 A
Switching current	1 A