



EE805A



Movement detector 360° flush mounted with normally open contact

Technical properties

Detection

Detection angle	360 - 360
Type of sensor	Movement detector, Presence detector

Settings

Time delay	5 S - 30 Min
------------	--------------

Lighting

Response brightness adjustable	5 - 1,000 lx
--------------------------------	--------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Width	19 mm
Built-in depth	55 mm
Recommended installation height	2.5 - 3.5 m

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Colour	White
Material	Plastic

Safety

Ingress Protection (IP) class	IP21
-------------------------------	------

Installation, mounting

Mounting on	Flush mounting
Suitable for outdoor usage	No

Texts

Function	Can only be used as individual unit
Installation mode	With spring clips for ceiling installation, For ceiling mounting
Type of connection	With plug-in terminals