



EER518

Motion detector highbay 360° surface mounted NO contact detection height 8m

Technical properties

Detection

Detection angle	360 - 360 °
Type of sensor	Movement detector

Settings

Time delay	1 Min - 1 h
------------	-------------

Lighting

Response brightness adjustable	5- 2,000 lx
--------------------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Built-in depth	78 mm
Recommended installation height	6 - 9 m

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Material	Plastic
----------	---------

Safety

Ingress Protection (IP) class	IP41
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No