



EHN010



Daily time switch 1 channel, 1 module

Technical properties

Equipment

Number of channels	1
--------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Power consumption during operation	1 W
230 V incandescent and halogen lamp	900 W
Power loss at full load	1 W

Functions

Number of function channels	1
-----------------------------	---

Connection

Number of contacts	1
Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1 - 6 mm ²

Use conditions

Operating temperature	-20 - +50 °C
-----------------------	--------------

Capacity

Number of modules	1
-------------------	---

Dimensions

Height	90 mm
Width	17.5 mm
Depth	60 mm

Texts

Switch mode	NO contact
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals

Electric current

Max. power (cos phi 0,6)	3 A
--------------------------	-----

Endurance

Electrical durability at nominal load in AC1 in operating cycles	50,000
---	--------

Voltage

Rated operational voltage U_e

230 - 240 V