




EHN111



## Daily time switch 1 channel, 3 modules with reserve

### Technical properties

#### Equipment

Number of channels	1
--------------------	---

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Power

Power consumption during operation	0.50 W
230 V incandescent and halogen lamp	1,100 W
Power loss at full load	1 W

#### Functions

Number of function channels	1
-----------------------------	---

#### Connection

Number of contacts	1
Cross-section flexible conductor	0.5 - 6 mm <sup>2</sup>
Cross-section rigid conductor	0.5 - 6 mm <sup>2</sup>

#### Use conditions

Operating temperature	-10 - +55 °C
-----------------------	--------------

#### Capacity

Number of modules	3
-------------------	---

#### Dimensions

Height	90 mm
Width	54 mm
Depth	60 mm

#### Texts

Switch mode	Change-over contact
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals

#### Electric current

Max. power (cos phi 0,6)	3 A
--------------------------	-----

#### Endurance

Electrical durability at nominal load in AC1 in operating cycles	50,000
---	--------

## Voltage

---

Rated operational voltage Ue

230 - 240 V