



Auxiliary contact for centralised control

Technical properties

Electric current

Rated current	1 A
---------------	-----

Capacity

Number of modules	0.50
-------------------	------

Use conditions

Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Power

Total power loss under IN	0.10 W
---------------------------	--------

Dimensions

Height	85 mm
Width	8.90 mm
Depth	58 mm