



## Auxiliary contact 1NC+1NO

### Technical properties

#### Electric current

Rated current	2 A
---------------	-----

#### Voltage

Rated insulation voltage $U_i$	250 V
--------------------------------	-------

#### Capacity

Number of modules	0.50
-------------------	------

#### Use conditions

Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Connection

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
Type of contacts	1NC+1NO

#### Power

Total power loss under IN	0.10 W
---------------------------	--------

#### Dimensions

Height	83 mm
Width	8.75 mm
Depth	58 mm