




EPN520



Latching relay 2NO 230V

Technical properties

Electric current

Rated current	16 A
Quiescent current	6 mA

Capacity

Number of modules	1
-------------------	---

Connection

Type of contacts	2NO
Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²
Number of contacts	2

Voltage

Command voltage AC	230 - 230 V
Command voltage DC	110 - 110 V
Command voltage 2	110 - 110 V
Command voltage 1	230 - 230 V
Rated insulation voltage Ui	250 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Power

Total power loss under IN	2.40 W
Inrush power absorbed	25 VA

Dimensions

Height	83 mm
Width	17.50 mm
Depth	63 mm

Lighting

Max. load fluorescent lamp	800 VA
----------------------------	--------