




EPN522



## Latching relay 2NO 8V

### Technical properties

#### Electric current

Rated current	16 A
Quiescent current	6 mA

#### Capacity

Number of modules	1
-------------------	---

#### Connection

Type of contacts	2NO
Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
Number of contacts	2

#### Voltage

Command voltage AC	8 - 8 V
Command voltage DC	0 - 0 V
Command voltage 1	8 - 8 V
Rated insulation voltage Ui	250 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Use conditions

Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C

#### Connectivity

Type of connection	Screw terminal
--------------------	----------------

#### Power

Total power loss under IN	2.40 W
Inrush power absorbed	25 VA

#### Dimensions

Height	83 mm
Width	17.50 mm
Depth	63 mm

#### Lighting

Max. load fluorescent lamp	800 VA
----------------------------	--------