



ESC126

## Contactor 25A, 1NC, 230V~50Hz

### Technical properties

#### Connection

Type of contacts	1NC
Number of contacts	1
Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1 - 10 mm <sup>2</sup>

#### Electric current

Rated current	25 A
---------------	------

#### Capacity

Number of modules	1
-------------------	---

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Voltage

Rated impulse withstand voltage Uimp	4,000 V
Rated insulation voltage Ui	250 V
Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V

#### Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

#### Endurance

Number of mechanical operations	100,000
Electric endurance in number of cycles	30,000

#### Power

Total power loss under IN	1.50 W
Inrush power absorbed	10.70 VA

#### Dimensions

Height	83 mm
Width	17.85 mm
Depth	60 mm

#### Equipment

Number of NO contacts	0
Number of NC contacts	1

**Installation, mounting**

---

Nominal tightening torque

1.20 - 1.20 Nm