



ESC263S



## Humfree Contactor 63A, 2NO, 230V~50/60Hz

### Technical properties

#### Connection

Type of contacts	2NO
Number of contacts	2
Cross-section flexible conductor	1.5 - 16 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 25 mm <sup>2</sup>

#### Electric current

Rated current	63 A
---------------	------

#### Capacity

Number of modules	3
-------------------	---

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Voltage

Rated impulse withstand voltage U <sub>imp</sub>	4,000 V
Rated insulation voltage U <sub>i</sub>	440 V
Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V

#### Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

#### Endurance

Number of mechanical operations	100,000
Electric endurance in number of cycles	30,000

#### Texts

Safety hint	Humfree contactors are not suitable for intensive use cases (powered 24/7) and in these cases industrial contactors must be used.
-------------	-----------------------------------------------------------------------------------------------------------------------------------

#### Power

Total power loss under I <sub>N</sub>	14.50 W
Inrush power absorbed	5.20 VA

#### Dimensions

Height	85 mm
Width	54 mm
Depth	60 mm

Equipment	
Number of NO contacts	2
Number of NC contacts	0
With switch for manual switch	No