



ESD425

Contactor 25A, 4NO, 24V~50Hz

Technical properties

Connection

Type of contacts	4NO
Number of contacts	4
Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1 - 10 mm ²

Electric current

Rated current	25 A
---------------	------

Capacity

Number of modules	2
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	4,000 V
Rated insulation voltage U _i	440 V
Rated operational voltage U _e	400 - 400 V
Command voltage AC	24 - 24 V
Command voltage DC	0 - 0 V

Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

Endurance

Number of mechanical operations	100,000
Electric endurance in number of cycles	30,000

Power

Total power loss under I _N	7.50 W
Inrush power absorbed	21 VA

Dimensions

Height	83 mm
Width	35.75 mm
Depth	60 mm

Equipment

Number of NO contacts	4
-----------------------	---

Number of NC contacts	0
With switch for manual switch	No

Installation, mounting

Nominal tightening torque	1.20 - 1.20 Nm
---------------------------	----------------