



EV106



Remote control dimmer 1-10V

Technical properties

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Connectivity

Dimming DALI	No
--------------	----

Power

Power consumption during operation	3 VA
------------------------------------	------

Power consumption standby	1 W
---------------------------	-----

Use conditions

Operating temperature	-10 - 45 °C
-----------------------	-------------

Dimensions

Height	85 mm
--------	-------

Width	71 mm
-------	-------

Depth	65 mm
-------	-------

Connection

Cross-section rigid conductor	1.5 - 10 mm ²
-------------------------------	--------------------------

Cross-section flexible conductor	1 - 6 mm ²
----------------------------------	-----------------------

Capacity

Number of modules	4
-------------------	---

Texts

Junction	Connection for illuminated (max. 5 mA) or standard push-buttons
----------	---

Type of connection	With screw terminals
--------------------	----------------------

Installation mode	For mounting on DIN rail
-------------------	--------------------------

Electric current

Control current 1-10 V slave	50 mA
------------------------------	-------

Materials

Colour	Grey
--------	------