



EVN011

Remote Control Dimmer universal 300W

Technical properties

Voltage	
Operating voltage	230 -230 V
Rated operational voltage Ue	230 - 230 V
Connectivity	
With bus system KNX radio	No
Frequency	
Frequency	50 - 60 Hz
Materials	
Colour	Grey
RAL code	7035
Material	Plastic
Dimensions	
Height	90 mm
Width	17.50 mm
Depth	65 mm
Architecture	
Control/operation element	Single push button
Power	
Power consumption during operation	2.10 VA
Power consumption standby	0.2 W
230 V incandescent and halogen lamp	300 W
Power incandescent lamp	300 - 300 W
Lighting	
Dimmable 230 V LED lamp	60 - 60 W
Use conditions	
Operating temperature	-10 - +45 °C
Connection	
Cross-section rigid conductor	1.5 - 6 mm²
Cross-section flexible conductor	1.5 - 6 mm²
Capacity	

Number of modules

Texts	
Dimming principle	Automatic load detection
Fuse	With electronic short-circuit and overload protection
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals