



FL31S

enclosure, univers, IP65, CL 2, 550 x 300 x 200mm, Polyester

**Technical properties**

**Dimensions**

Height	550 mm
Width	300 mm
Depth	300 mm
Thickness of sidewall	2 mm

**Safety**

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	3-point lever, 4-side 8 mm
Impact resistance IK	IK10

**Equipment**

Number of section in width	1
Number of flange plate openings	0
Number of rows	3

**Installation, mounting**

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Varnished
Material	Glass reinforced polyester
Surface finish	Mat

**Cover, door**

Number of cabinet doors	1
Number of locks	1
Door/cover is transparent	No

**Electric current**

Rated current	400 A
---------------	-------

**Voltage**

Nominal voltage	230 - 400 V
-----------------	-------------