



FL327B

Polyester floor standing enclosure, Orion.Plus, plain door 1200x850x300 mm

Technical properties

Dimensions

Height	1,200 mm
Width	850 mm
Depth	300 mm
Thickness of sidewall	2 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	Barrel lock, Key lock
Impact resistance IK	IK08

Equipment

Number of section in width	1
Number of flange plate openings	0
Number of rows	7

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

Materials

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Glass reinforced polyester

Cover, door

Number of cabinet doors	0
Door/cover is transparent	No

Electric current

Rated current	630 A
---------------	-------