



FL358B

Polyester double enclosure, Orion.Plus, plain door 2050x850x300 mm

Technical properties

Dimensions

Height	2,050 mm
Width	850 mm
Depth	300 mm
Thickness of sidewall	1.50 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	3-Side 7 mm, Key lock
Impact resistance IK	IK10

Equipment

Number of section in width	1
Number of flange plate openings	0
Number of rows	12

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

Materials

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Plastic

Cover, door

Number of cabinet doors	0
Door/cover is transparent	Yes

Electric current

Rated current	630 A
---------------	-------