



FL510B

**Polyester wall mounting enclosure, Orion.Plus, 550x1100x300 mm**

**Technical properties**

**Dimensions**

Height	550 mm
Width	1,100 mm
Depth	300 mm
Thickness of sidewall	1.50 mm

**Safety**

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	3-Side 7 mm, Key lock
Impact resistance IK	IK08

**Equipment**

Number of section in width	2
Number of flange plate openings	0
Number of rows	3

**Installation, mounting**

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Plastic

**Cover, door**

Number of cabinet doors	0
Door/cover is transparent	Yes

**Electric current**

Rated current	630 A
---------------	-------