



FL511B

Polyester wall mounting enclosure, Orion.Plus, 850x1100x300 mm

Technical properties

Dimensions

| | |
|-----------------------|----------|
| Height | 850 mm |
| Width | 1,100 mm |
| Depth | 300 mm |
| Thickness of sidewall | 1.50 mm |

Safety

| | |
|-------------------------------|-----------------------|
| Ingress Protection (IP) class | IP65 |
| Protection class | Isolation class II |
| Locking type | 3-Side 7 mm, Key lock |
| Impact resistance IK | IK08 |

Equipment

| | |
|---------------------------------|---|
| Number of flange plate openings | 0 |
| Number of rows | 5 |

Installation, mounting

| | |
|----------------------------|---------------|
| Mounting on | Wall mounting |
| Suitable for outdoor usage | Yes |

Materials

| | |
|-----------|------------|
| Colour | Light grey |
| RAL code | 7035 |
| Treatment | Untreated |
| Material | Plastic |

Cover, door

| | |
|---------------------------|-----|
| Number of cabinet doors | 0 |
| Door/cover is transparent | Yes |

Electric current

| | |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|