



FL526B

Polyester floor standing enclosure, Orion.Plus, 900x850x300 mm

Technical properties

Dimensions

Height	900 mm
Width	850 mm
Depth	300 mm
Thickness of sidewall	1.50 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	3-Side 7 mm, Key lock
Impact resistance IK	IK08

Equipment

Number of flange plate openings	0
Number of rows	5

Installation, mounting

Mounting on	Floor mounting
Suitable for outdoor usage	Yes

Materials

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Plastic

Cover, door

Number of cabinet doors	0
Door/cover is transparent	Yes

Electric current

Rated current	630 A
---------------	-------