



FL72S

enclosure, univers, IP65, CL 2, 1150 x 600 x 300mm, Polyester

Technical properties

Dimensions

Height	1,150 mm
Width	600 mm
Depth	300 mm
Thickness of sidewall	2 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	3-point lever, 4-side 8 mm
Impact resistance IK	IK10

Equipment

Number of section in width	2
Number of flange plate openings	0
Number of rows	7

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

Materials

Colour	Light grey
RAL code	7035
Treatment	Varnished
Material	Glass reinforced polyester
Surface finish	Mat

Cover, door

Number of cabinet doors	1
Number of locks	1
Door/cover is transparent	No

Electric current

Rated current	400 A
---------------	-------