



FP25TN2

Enclosure, univers, IP44,Protecion class 1, 1950x1300x205mm, empty

Technical properties

Dimensions

Height	1,950 mm
Width	1,300 mm
Depth	205 mm
Thickness of sidewall	1 mm

Safety

Ingress Protection (IP) class	IP44
Protection class	Isolation class I
Locking type	3-point lever, Key lock
Impact resistance IK	IK09

Equipment

Number of section in width	5
Number of flange plate openings	10
Number of rows	12

Installation, mounting

Mounting on	Floor mounting
Suitable for outdoor usage	No

Materials

Colour	Pure white
RAL code	9010
Treatment	Powder coated
Material	Steel

Cover, door

Number of cabinet doors	2
Number of locks	0
Door/cover is transparent	No

Electric current

Rated current	400 A
---------------	-------