



FR11E1

Steel enclosure, Univers, IP55, CL1, 1700x300x275 mm, plinth H100 mm

#### Technical properties

##### Dimensions

Height	1,800 mm
Width	300 mm
Depth	275 mm
Thickness of sidewall	1.50 mm

##### Safety

Ingress Protection (IP) class	IP55
Protection class	Isolation class I
Locking type	Without lock
Impact resistance IK	IK10

##### Equipment

Number of section in width	1
Number of flange plate openings	2
Number of rows	11

##### Installation, mounting

Mounting on	Floor mounting
Suitable for outdoor usage	No

##### Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel
Surface finish	Mat

##### Cover, door

Number of cabinet doors	1
Number of locks	1
Door/cover is transparent	No

##### Electric current

Rated current	800 A
---------------	-------

##### Voltage

Nominal voltage	690 - 690 V
-----------------	-------------