



FR24K2

Steel enclosure, Univers, IP55, CL1, 1850x1050x275 mm, plinth H200 mm

#### Technical properties

##### Dimensions

|                       |          |
|-----------------------|----------|
| Height                | 2,050 mm |
| Width                 | 1,050 mm |
| Depth                 | 275 mm   |
| Thickness of sidewall | 1.50 mm  |

##### Safety

|                               |                   |
|-------------------------------|-------------------|
| Ingress Protection (IP) class | IP55              |
| Protection class              | Isolation class I |
| Locking type                  | Without lock      |
| Impact resistance IK          | IK10              |

##### Equipment

|                                 |    |
|---------------------------------|----|
| Number of section in width      | 4  |
| Number of flange plate openings | 8  |
| Number of rows                  | 12 |

##### Installation, mounting

|                            |                |
|----------------------------|----------------|
| Mounting on                | Floor mounting |
| Suitable for outdoor usage | No             |

##### Materials

|                |               |
|----------------|---------------|
| Colour         | Light grey    |
| RAL code       | 7035          |
| Treatment      | Powder coated |
| Material       | Steel         |
| Surface finish | Mat           |

##### Cover, door

|                           |     |
|---------------------------|-----|
| Number of cabinet doors   | 2   |
| Number of locks           | 1   |
| Door/cover is transparent | Yes |

##### Electric current

|               |       |
|---------------|-------|
| Rated current | 800 A |
|---------------|-------|

##### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 690 - 690 V |
|-----------------|-------------|