



FR25G2

Steel enclosure, Univers, IP55, CL1, 1850x1300x400 mm, plinth H200 mm

Technical properties

Dimensions

Height	2,050 mm
Width	1,300 mm
Depth	400 mm
Thickness of sidewall	1.50 mm

Safety

Ingress Protection (IP) class	IP55
Protection class	Isolation class I
Locking type	Without lock
Impact resistance IK	IK10

Equipment

Number of section in width	5
Number of flange plate openings	10
Number of rows	12

Installation, mounting

Mounting on	Floor mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel
Surface finish	Mat

Cover, door

Number of cabinet doors	2
Number of locks	1
Door/cover is transparent	No

Electric current

Rated current	800 A
---------------	-------

Voltage

Nominal voltage	690 - 690 V
-----------------	-------------