



FWU42S

FW flush encl. 4-rows 96 modules, IP30, classII, niche 657x565x115mm

Technical properties

Connection

Number of conduit inlets	4
--------------------------	---

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting, Hollow wall

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	8
Number of rows	4
Number of section in width	2
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

Capacity

Number of modules	96
-------------------	----

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	703 mm
Width	603 mm
Depth	125 mm
Built-in height	652 mm
Built-in width	560 mm
Built-in depth	112 mm
Number of width units	24

Cover, door

Number of cabinet doors	1
Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connectivity

Subject to technical modifications

Mounting type	Screw mounting
Materials	
Material	Steel
RAL code	9010
Colour	Pure white
Safety	
Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	850 °C