



FWU73S

FW flush encl. 7-rows 252 modules, IP30, classII, niche 1107x815x115mm

Technical properties

Connection

Number of conduit inlets	6
--------------------------	---

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting, Hollow wall

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	21
Number of rows	21
Number of section in width	3
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

Capacity

Number of modules	252
-------------------	-----

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	1,153 mm
Width	853 mm
Depth	125 mm
Built-in height	1,102 mm
Built-in width	810 mm
Built-in depth	112 mm
Number of width units	36

Cover, door

Number of cabinet doors	2
Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connectivity

Mounting type

Screw mounting

Materials

Material

Steel

RAL code

9010

Colour

Pure white

Safety

Protection class

Isolation class II

Impact resistance IK

IK09

Ingress Protection (IP) class

IP30

Locking type

Without lock

Glow wire test

850 °C