



HFD312

**Fuse comb. switch 3P - 125 A /T00**

**Technical properties**

**Electric current**

Rated current	125 A
---------------	-------

**Architecture**

Number of poles	3
Control/operation element	Door coupling rotary drive

**Voltage**

Rated insulation voltage Ui	750 V
-----------------------------	-------

**Power**

Total power loss under I <sub>N</sub>	60.90 W
Power loss per pole at I <sub>N</sub>	20.30 W
Rated operational power under 400 V AC AC1	82,000 W

**Safety**

Ingress Protection (IP) class	IP00
-------------------------------	------

**Fuse**

Fuse size	NH00
-----------	------

**Dimensions**

Height	162 mm
Width	148 mm

**Cover, door**

Interlockable	Yes
---------------	-----