



HIM306

Modular change-over switch 3x63A

Technical properties

Voltage

Rated operational voltage Ue	380 - 415 V
Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8,000 V

Electric current

Rated current	63 A
Rated short-time withstand current Icw IEC 60947	1.50 kA
Rated conditional short-circuit current Icc with gI-gG fuses	50 kA

Power

Rated operational power under 400 V AC AC1	41,000 W
Total power loss under IN	4.50 W

Architecture

Number of poles	3
Control/operation element	Short rotary handle
Type of pole	3P

Dimensions

Height	93.5 mm
Width	105 mm
Depth	110 mm

Controls and indicators

Motor drive integrated	No
------------------------	----

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Capacity

Number of modules	6
-------------------	---

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature

-20 - 70 °C

Connection

Cross-section flexible conductor

2.5 - 35 mm²

Cross-section rigid conductor

2.5 - 35 mm²