



JN216BG

250A 16 Way 125A Outgoers Glazed

Technical properties

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	250 A
---------------	-------

Equipment

With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes

Dimensions

Height	1,550 mm
Width	710 mm
Depth	178.40 mm

Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

Materials

Material	Steel
RAL code	7035, 9001
Colour	Light grey

Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock, Quarter turn lock