



Insulated busbar 3P 63A prong 10mm² 57M

Technical properties

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	3
-----------------	---

Dimensions

Length	1,000 mm
--------	----------

Voltage

Rated impulse withstand voltage U _{imp}	4,000 V
--	---------

Rated operational voltage U _e	230 - 400 V
--	-------------

Connection

Cross-section rigid conductor	10 mm ²
-------------------------------	--------------------

Connector/plug type	Phase busbar with pin
---------------------	-----------------------

Capacity

Number of modules	57
-------------------	----

KB363B