



KB363C

Insulated busbar 3P 63A prong 10mm² 24M

Technical properties

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	3
-----------------	---

Dimensions

Length	420 mm
--------	--------

Voltage

Rated impulse withstand voltage Uimp	4,000 V
--------------------------------------	---------

Connection

Cross-section rigid conductor	10 mm²
Connector/plug type	Phase busbar with pin

Capacity

Number of modules	24
-------------------	----