



Insulated busbar 3P+N 63A prong 10mm² 48C for MCB 1P+N 1 module

Technical properties

Electric current

Rated current 63 A

Architecture

Number of poles 4

Dimensions

Length 428 mm

Voltage

Rated impulse withstand voltage U_{imp} 4,000 V

Connection

Cross-section rigid conductor 10 mm²

Connector/plug type Phase busbar with pin

Capacity

Number of modules 24

KBN663C