



Insulated busbar 1P 80A fork 16mm² 12M

Technical properties

Electric current

Rated current	80 A
---------------	------

Architecture

Number of poles	1
-----------------	---

Dimensions

Length	210 mm
--------	--------

Voltage

Rated impulse withstand voltage Uimp	4,500 V
--------------------------------------	---------

Connection

Cross-section rigid conductor	16 mm²
Connector/plug type	Phase busbar with fork

Capacity

Number of modules	12
-------------------	----

KDN180A